



- 3 Type**
- A** Mounting from the back (threaded blind bore)
  - B** Mounting from the operator's side (only for  $d_1 = 28$ )

d <sub>1</sub>	Length l ±0,25								d <sub>2</sub>	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	b <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
	180	200	250	300	350	400	500	600								
20	180	200	250	300	350	400	-	M 6	24	12	42	54	42	54	12	
28	200	250	300	350	400	500	600	M 8	25	14	50	66	50	66	15	
30	200	300	350	400	500	600	1000	M 8	27	17	51	68	51	68	15	

**Specification**

**Handle tube**

- Aluminium, wall thickness 1,5 mm
- Powder coated
  - Black RAL 9005, textured finish
  - Handle legs black
- Anodized, natural color
  - Handle legs black
- Anodized, natural color
  - Handle legs silver

- **SW**
- **EL**
- **ES**

**Handle legs**

- Zinc die casting
- Powder coated, textured finish
- Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

**Cover**

Plastic, light gray

**Cover cap for type B**

- Plastic
- Black for SW / EL
- Light gray for ES

RoHS

The handle tube of the GN 333 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

A typical application area for tubular handles GN 333 are double-winged doors at machines or devices.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.8.

see also...	Page
GN 333.1 Tubular Handles (Straight)	QVX
GN 332 Tubular Handles (with Power Switching Function)	QVX

**Technical Information**

Load Rating Information	QVX
-------------------------	-----

**Accessory**

GN 333.8 Handle Legs (for Tubes Ø 28, Straight)	QVX
---	-----

How to order	
1	d <sub>1</sub>
2	Length l
3	Type
4	Finish

**GN 333-28-600-A-EL**

