


x = ground

Application example

Clamping pad
GN 709.1



Positioning element
GN 409.2



3 Type

- B** Smooth contact face
- K** Spherical contact face
- R** Serrated contact face

1

2

h Type B: ±0,01 Type K / R: ±0,1	d ₁	d ₂ Type B / R	Length l	A/F	e Width across corners
10	M 8	17	10	17	19,4
10	M 10	19	12	19	21,9
10	M 12	22	14	22	25,2
15	M 10	19	12	19	21,9
15	M 12	22	14	22	25,2
15	M 16	30	19	30	34,2
20	M 16	30	19	30	34,2

Specification

- Steel
 - Case-hardened
 - Blackened
- RoHS

Information

Positioning elements GN 409.1 with threaded stud are designed for use as locating plungers, stops and thrust blocks.

see also...

- *Workholding Bolts / Headed Dowels GN 409.1* → Page 1116
- *Guide Bushings DIN 172 / DIN 179* → Page 1112

How to order

GN 409.1-15-M10-B

1	h
2	d ₁
3	Type

