



EDELSTAHL® Rostfrei
Inox
Stainless
Steel

1.1

1.2

1.3

1.4

¹ d ₁	² Length l ±0,5						b ₁	b ₂	d ₂	h ₁	h ₂	t min.
28	200	250	300	400	500	600	25	14	M 8	50	66	15

2.1

Specification

- Handle tube Ø 28 x 2
Stainless steel AISI 304
Ground, matte shiny finish
- Handle legs
Stainless steel precision casting AISI CF-8
Matte shot-blasted
- *Load Rating Information* → Page 2106
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

With the stainless steel tubular handles GN 333.7, the handle legs and the handle tube are pressed together.

see also...

- *Stainless Steel Cabinet U-Handles GN 426.5* → Page 155
- *Stainless Steel Cabinet U-Handles GN 565.5 (Mounting from the Back or the Operator's Side)* → Page 108
- *Stainless Steel Tubular Handles GN 666.5 (Mounting from the Back)* → Page 206
- *Tubular Handles GN 333 (Aluminum, Zinc Die Casting)* → Page 186

2.2

2.3

2.4

How to order		1	d ₁
GN 333.7-28-400		2	Length l

