



1.1

1.2

1.3

1.4

1 2

b ₁		l ₁ ±0,5								a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
36	200	250	300	350	400	500	600	800	24	38	8,5	57	72	5	14,5	7,5	41	

2.1

Specification

3

- Handle tube
Aluminum

- Handle legs
Zinc die casting
Powder coated

- Tube ● SW
Powder coated
Black, RAL 9005, textured finish
Handle legs
Black, RAL 9005, textured finish

- Tube ● EL
Anodized, natural color
Handle legs
Black, RAL 9005, textured finish

- Tube ● ES
Anodized, natural color
Handle legs
Silver, RAL 9006, textured finish

- Cover
Plastic, light gray

- Load Rating Information → Page 2106

- RoHS

Information

Oval tubular handles GN 334.1 are highly stable.
The handle tube can be mounted without any further machining, allowing **special lengths** to be realised easily.

see also...

- Product Family Standard Parts for Profile Systems → Page 18
- Assembly Sets for Profile Systems 30 / 40 GN 965 → Page 2086
- Assembly Sets for Profile Systems 30 / 40 / 45 GN 968 → Page 2096

2.2

2.3

2.4

How to order

GN 334.1-36-400-ES

1	b
2	l ₁
3	Finish

