



1.1

1.2

1.3

1.4

1

2

d ₁	d ₂		d ₃ ≈	h	t _{min.}
20	M 5	M 6	12	30	18
25	M 6	M 8	15	38	18
30	M 8	M 10	18	46	18
35	M 10	M 12	21	53	21

2.1

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 110 °C
- Black, shiny finish

• *Plastic Characteristics* → Page 2158

• RoHS

2.2

2.3

2.4

How to order

GN 419-25-M8

1 d₁

2 d₂

