



<div>2</div> <div>d_1</div>	<div>3</div> <div>d_2</div>	<div>4</div> <div>l_1</div>			l_2	A/F_1	A/F_2	t	Static load in kN (see information)
14	M 8	44	69	-	21	16	3	5	2,7
14	M 10	44	69	99	21	16	4	6	4,8
14	M 12	44	69	99	21	16	5	7	6,8

Specification	<div>1</div>
Plastic , polyamide (PA-HP)	PA
• Glass fiber reinforced	
• Operating temperature -30 °C to +100 °C	
• Black, matte finish	
RoHS	
Accessory	Page
GN 3441 Base Plates (Plastic)	QVX

Threaded studs GN 3440 are made of plastic, making them lightweight, resistant to corrosion and electrically insulating. They are used with base plates GN 3441 for setting up and leveling machines, devices and equipment.	
The static load capacity values specified in the table are non-binding guidelines; exceeding these values may result in deformation or component failure.	
see also...	Page
GN 3440 Threaded Studs (Steel / Stainless Steel)	QVX
GN 3440.1 Ball Joints	QVX

Technical Information	
Overview of Combinability	QVX
Plastic Characteristics	QVX

How to order	<div>1</div> Material
<div>1</div>	<div>2</div> d_1
<div>2</div>	<div>3</div> d_2
<div>3</div>	<div>4</div> l_1
GN3440-PA-14-M12-44	