



Length l	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	F <sub>1</sub> Static load in N folded out
100	34	44,5	55	500
120	34	44,5	55	500
180	34	44,5	55	500

**Specification**



**Handle**

- Steel, chrome plated
- Stainless steel AISI 303
- Matte, shot-blasted

● CR  
NI

**Attachment part**

- Plastic, Polyamid (PA)
- Operating temperature up to 100 °C
- Black, matte finish

**Cover**

- Plastic, Polyamid (PA)
- Operating temperature up to 100 °C
- Black-gray, matte finish

RoHS

Folding handles GN 425.5 are used in places where the handle must not protrude or protrude only a short distance.

The handle is locked in place in the resting position by means of a spring-loaded (disk springs) thrust bolt.

The static load capacity value given in the table is an approximate value which, if exceeded, may result in permanent deformation or fracture of the plastic attachment part. The folding handle GN 425.2 may be used as an alternative.

see also...

Page

**GN 425.8** Folding Handles with Recessed Tray (with Handle Locking or Spring-Loaded Return) QVX

**GN 425.2** Folding Handles QVX

**GN 825.1** Folding Handles (Plastic, with Spring-Loaded Return) QVX

**Technical Information**

Load Rating Information QVX

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order

**GN 425.5-100-CR**

1 Length l

2 Finish (Material)

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

