



Length l	h ₁	h ₂	h ₃	F ₁ Static load in N folded out
100	34	44,5	55	500
120	34	44,5	55	500
180	34	44,5	55	500

Specification

Handle

- Steel, chrome plated
- Stainless steel AISI 303
- Matte, shot-blasted

© CR NI

Attachment part

- Plastic, polyamide (PA)
- Operating temperature up to 100 °C
- Black, matte finish

Cover

- Plastic, polyamide (PA)
- Operating temperature up to 100 °C
- Black-gray, matte finish

RoHS

Folding handles GN 425.5 are used in places where the handle must not protrude or protrude only a short distance.

The handle is locked in place in the resting position by means of a spring-loaded (disk springs) thrust bolt.

The static load capacity value given in the table is an approximate value which, if exceeded, may result in permanent deformation or fracture of the plastic attachment part. The folding handle GN 425.2 may be used as an alternative.

see also...	Page
GN 425.8 Folding Handles with Recessed Tray (with Handle Locking or Spring-Loaded Return)	QVX
GN 425.2 Folding Handles	QVX
GN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 425.5-100-CR

- 1 Length l
- 2 Finish (Material)