



1	2	3													
d ₁	d ₂	l ₁			d ₃	k	l ₂	l ₃	l ₄	A/F ₁	A/F ₂	Ball Ø	Static load in kN (see information)		
80	M 8	44	69	-	8,5	54	35	23	24	16	3	14	2,7		
80	M 10	44	69	99	8,5	54	35	23	24	16	4	14	4,8		
80	M 12	44	69	99	8,5	54	35	23	24	16	5	14	6,8		
100	M 8	44	69	-	12,5	70	36	23	24	16	3	14	2,7		
100	M 10	44	69	99	12,5	70	36	23	24	16	4	14	4,8		
100	M 12	44	69	99	12,5	70	36	23	24	16	5	14	6,8		

Specification

- Base plate**
Plastic, polyamide (PA)
 - Glass fiber reinforced
 - Black, matte finish
- Threaded stud**
Plastic, polyamide (PA-HP)
 - Glass fiber reinforced
 - Black, matte finish
- Rubber pad** for type AG
Acrylonitrile butadiene rubber (NBR)
Hardness 70 Shore A, black
- Operating temperature** -30 °C to +100 °C
- RoHS

Leveling feet GN 345.9 are made of plastic, making them lightweight, resistant to corrosion and electrically insulating. They are used for setting up and leveling machines, devices and equipment. The geometry of the base plate distributes the load over a large area and, in combination with the high-quality plastic, results in a high static load capacity. The leveling feet are supplied assembled, but they can also be taken apart.

The leveling feet are supplied assembled, but they can also be taken apart. The mounting holes in the base plate are sealed with a thin layer of plastic when delivered, which can be easily pierced or drilled through. The static load capacity values specified in the table are non-binding guidelines; exceeding these values may result in deformation or component failure.

Technical Information	Page
Plastic Characteristics	QVX

see also...	Page
GN 345 Leveling Feet (Plastic, Threaded Stud Steel)	QVX
GN 345.5 Leveling Feet (Plastic, Threaded Stud Stainless Steel)	QVX

How to order

1	d ₁
2	d ₂
3	l ₁
4	Type

GN345.9-80-M8-44-AG