



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

1 d_1	2 l_1 <small>±0,5 Type A</small> <small>±0,3 Type B Threaded bore for mounting stud</small>	d_2	d_3	h	l_2	r	t_1	t_2
20	200	M 8	-	68	20	22	15	-
20	250	M 8	-	68	20	22	15	-
20	300	M 8	-	68	20	22	15	-
20	350	M 8	-	68	20	22	15	-
28	250	M 10	32	90	20	32	-	17
28	300	M 10	32	90	20	32	-	17
28	350	M 10	32	90	20	32	-	17
28	400	M 10	32	90	20	32	-	17

Specification

Handle

- Stainless steel AISI 304
- $d_1 = 20$: Solid material
- $d_1 = 28$: Tube $\varnothing 28 \times 2$
- Matte shot-blasted

Threaded bushing / Mounting stud

Stainless steel AISI 303

Grub screw for type B

Stainless steel

- $d_1 = 20$: DIN 914-M5-6-NI
- $d_1 = 28$: DIN 914-M6-8-NI

RoHS

Cabinet U-handles GN 426.5 can be mounted from the back (type A) as well as from the operator's side (type B). In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the grub screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l_2 might be required.

see also...

	Page
GN 426 Cabinet U-Handles (Aluminum)	QVX
GN 666.5 Tubular Handles	QVX
GN 666.7 Tubular Handles	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order

GN 426.5-28-400-A

1 d_1	
2 l_1	
3 Type	