



1 d_1		2 d_2		3 h_1	b	d_3	d_4 For screw	h_2	m
45	M 6	M 8	16	25	15	M 6	6	30	
60	M 10	M 12	24	30	21,5	M 8	6	40	

Specification

- Steel precision casting
- Zinc plated, blue passivated **ZB**
- Zinc plated and powder coated Black, RAL 9005, textured finish **● SW**
- RoHS

4 Information

Threaded flanges GN 3490 are used in connection with T-slot profile systems and allow elements to be assembled on or underneath the profiles, e.g. levelling feet.

Depending on the threaded flange, thread size and thread depth dimensions that are available can exceed the dimensions of the profile groove.

see also...

- *Product Family Standard Parts for Profile Systems* → Page 18
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order	1 d_1
	2 d_2
	3 h_1
	4 Finish

1 2 3 4
GN 3490-45-M8-16-SW