


**3 Type**  
**B** Mounting on both sides

Application example



<b>1</b> $b_1$	<b>2</b> $d_1$	$b_2$	$d_2$ For screw	$h_1$	$h_2$	Length $l$	$m_1$	$m_2$	$m_3$
8	M 4	7	M 3	2,5	9,5	25	6	16	1,5
10	M 5	8	M 4	3,5	12	32	8	20	2
12	M 6	10	M 5	4	15	38	10	24	2,5
16	M 8	13	M 6	5	18,5	47	12	30	3
20	M 10	16	M 8	6	23	60	15	38	4

**Specification**

- Stainless steel precision casting AISI CF-8 **NI**  
 Matte shot-blasted finish **GS**
- Stainless Steel Characteristics → Page QVX
- RoHS

**Information**

Mounting blocks GN 3492 quickly and easily fasten standard parts with external thread, such as spring plungers or setting bolts, perpendicular to the mounting plane. The slotted holes and the locating thread allow for positioning of the mounting blocks in two directions.

To prevent unintentional adjustment, the standard part can be secured with a clamping thread lock, a lock nut or a grub screw.

see also...

- Product Family Standard Parts for Profile Systems → Page QVX
- Spring Plungers GN 615.3 (with Ball, with Internal Hex) → Page QVX
- Spring Plungers GN 615 (with Ball, with Slot) → Page QVX
- Threaded Flanges GN 3490 → Page QVX

How to order

<b>1</b>	$b_1$
<b>2</b>	$d_1$
<b>3</b>	Type
<b>4</b>	Material
<b>5</b>	Finish

**GN 3492-12-M6-B-NI-GS**

