



Type A




Type B




Assembly examples

as spacer disk



as foot disk



4 Type

- A Mounting with fixing hole
- B Mounting with adhesive pad

1

2

3

d ₁	h			d ₂ +0,5	d ₃ +0,5	s ₁	s ₂
19	3	7	14	4	7,5	1,5	1,1
25	3	8	16	4	7,5	1,5	1,1
32	4	9	18	5	9	2	1,1
38	4	10	20	5	9	2	1,1
50	5	11	22	6	11	2,5	1,1
64	5	13	26	6	11	2,5	1,1

Specification

5

- **GN 438**
Steel
Zinc plated, blue passivated
- **GN 438.5**
Stainless steel AISI 304
- Rubber underlay
Acrylonitrile butadiene rubber (NBR)
- Vulcanized
- Black
- Temperature resistant up to 120 °C
- Hardness Shore A **70**
- Adhesive pad (only type B)
Scotch mount TM 5952
- Double-sided
- Acrylate rubber core
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Other Shore hardnesses

Information

Spacer disks and foot disks GN 438 / GN 438.5 provide a damping and muffling function and protect surfaces from damage.

By stacking several spacer disks on each other, the spring rate of the package can be increased, which opens up new possibilities for use.

Foot discs are used for installing small machines, systems or devices and, for the type A, are attached with screws. Bear in mind the maximum height of the screw head. Alternatively, after the protective film has been removed, the type B can be adhered to all suitable and clean surfaces by means of the adhesive pad.

see also...

- *Buffers GN 454* → Page 1532

How to order (Steel)

1	d ₁
2	h
3	d ₂
4	Type
5	Hardness

GN 438-25-16-4-A-70

How to order (Stainless steel)

1	d ₁
2	h
3	d ₂
4	Type
5	Hardness

GN 438.5-64-26-6-B-70