



1 2 3

d ₁	d ₂	h ₁		d ₃	h ₂		h ₃		for screw	Static load F in kN				Code no. C-Spanner
		Version Low	Version High		Version Low	Version High	Version Low	Version High		F ₁ *	F ₂ **	F ₁ *	F ₂ **	
25	6,6	22	35	M 15 x 1	26	50	4	15	M 6	40	30,7	27,1	20,26	DIN 1810-A25-28
32	6,6	26	43	M 20 x 1	31	63	5	20	M 6	65	55,7	43,4	36,56	DIN 1810-A30-32
32	9	26	43	M 20 x 1	31	63	5	20	M 8	65	48	43,4	30,86	DIN 1810-A30-32
32	11	26	43	M 20 x 1	31	63	5	20	M 10	65	37,9	43,4	23,41	DIN 1810-A30-32
45	11	34	54	M 30 x 1,5	41	79	7	25	M 10	120	92,9	84	64,01	DIN 1810-A45-50
45	13,5	34	54	M 30 x 1,5	41	79	7	25	M 12	120	80,4	84	54,82	DIN 1810-A45-50
45	17,5	34	54	M 30 x 1,5	41	79	7	25	M 16	120	45,5	84	28,90	DIN 1810-A45-50
58	17,5	44	70	M 40 x 1,5	53	102	9	32	M 16	210	136	148	92,90	DIN 1810-A58-62
58	22	44	70	M 40 x 1,5	53	102	9	32	M 20	210	90	148	59,08	DIN 1810-A58-62
58	26	44	70	M 40 x 1,5	53	102	9	32	M 24	210	37	148	20,30	DIN 1810-A58-62
70	22	50	83	M 50 x 1,5	60	123	10	40	M 20	330	210	225	136,08	DIN 1810-A68-75
70	26	50	83	M 50 x 1,5	60	123	10	40	M 24	330	157	225	97,30	DIN 1810-A68-75
70	33	50	83	M 50 x 1,5	60	123	10	40	M 30	330	53	225	20,60	DIN 1810-A68-75
80	26	56	94	M 60 x 2	68	144	12	50	M 24	495	322	323	195,30	DIN 1810-A80-90
80	33	56	94	M 60 x 2	68	144	12	50	M 30	495	218	323	118,60	DIN 1810-A80-90
80	39	56	94	M 60 x 2	68	144	12	50	M 36	495	101	323	38,20	DIN 1810-A80-90

* max. total load ** max. load after deduction of the max. preload, for ST for screws 8.8 (μ = 0,125), for NI for screws 6.8 (μ = 0,14)

Specification

Steel 1.7225 (42 CrMo 4 V) **ST**
Zinc plated, blue passivated

Stainless steel AISI 303 (X 10 CrNiS 18-9) **NI**

RoHS

Accessory

DIN 1810 C-Spanner **QVX**
(Code no. see table)

Leveling sets GN 350.2 are used for leveling, adjusting and linking operations. The spherical washer allows precise installation of two non parallel planes at a required gradient up to ≈ 4°.

They comprise a threaded upper sleeve and an internal threaded lower sleeve. The fine thread allows a stepless and precise setting and locking using the C-Spanner DIN 1810. A locking ring serves as a height limiter for the max. height.

see also...	Page
GN 350 Leveling Sets (High Type)	QVX
GN 350.1 Leveling Sets (Low Type)	QVX

Technical Information

Strength Values of Screws	QVX
Stainless Steel Characteristics	QVX

How to order	1 d ₁
	2 d ₂
	3 h ₁
GN 350.2-32-11-43-NI	4 Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

