



**Rost frei**®  
Inox  
Stainless  
Steel

**4 Type**

- A** Without lock nut
- B** With lock nut

1 $d_1$ Support plate		2 $d_2$	3 $h_1$ max.	$d_3$	$d_4$	$h_2$ min.	$h_3$ Adjustable range	$h_4$ min.	$h_5$ Adjustable range	Static load F in kN		Code no. C-Spanner
$d_1 = d_4$	$d_1 > d_4$									ST	NI	
40	79	M 10	69	M 28 x 1,5	40	53	16	59	10	100	70	DIN 1810-A40-42
40	79	M 10	86	M 28 x 1,5	40	62	24	68	18	100	70	DIN 1810-A40-42
52	99	M 12	80	M 36 x 1,5	52	61	19	69	11	125	85	DIN 1810-A52-55
52	99	M 12	103	M 36 x 1,5	52	73	30	80	23	125	85	DIN 1810-A52-55
65	119	M 16	112	M 45 x 1,5	65	82	30	90	22	225	155	DIN 1810-A65-70
65	119	M 16	148	M 45 x 1,5	65	100	48	108	40	225	155	DIN 1810-A65-70

**Specification**

- Steel **ST**
- Zinc plated, blue passivated
- Stainless steel AISI 304 **NI**
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Accessory**

- C-Spanner DIN 1810  
(code no. see table)

**Information**

Leveling sets GN 360 are used for leveling and to compensate for any slope when setting up machines and systems.

The thread  $d_2$  can also be used as a through-hole for attachment from below. The fine thread  $d_3$  allows precise adjustment and readjustment using a DIN 1810 C-Spanner. A circlip limits the maximum path of adjustment.

see also...

- *Leveling Sets GN 350 / GN 350.1* → Page 1134 / 1135
- *Leveling Sets GN 350.2 / GN 350.5* → Page 1136 / 1137

How to order	
1	$d_1$
2	$d_2$
3	$h_1$
4	Type
5	Material

**GN360-119-M16-148-A-ST**