



1 d_1	2 h_1	3 d_2	d_3 Through hole for screw	h_2	h_3	t min.	Static load capacity in kN
16	16	M 4	M 3	11	4	8	0,25
16	24	M 4	M 3	19	4	8	0,25
20	20	M 5	M 4	14	4	10	0,4
20	30	M 5	M 4	24	4	10	0,4
25	25	M 6	M 5	17	4,7	12	0,7
25	40	M 6	M 5	32	4,7	12	0,7
32	32	M 8	M 6	23	5,7	16	1,6
32	50	M 8	M 6	41	5,7	16	1,6

Specification	5	6
Base body		
• Aluminum	AL	S
• Turned, anodized, black		
• Stainless steel AISI 316L	A4	M
• Turned		

Cover cap	
Thermoplastic elastomer (TPE)	
• Hardness \approx 75 Shore A	
• Black	

RoHS

On request	
• $d_1 = 25 / 32$ in stainless steel with ESD cover cap	

Technical Information	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Equipment feet GN 440 are used to set up devices, smaller machines, or fixtures, on worktops or tables. The non-slip cover cap increases stability, reduces wear on the underlying surface and covers the mounting hole from below.

They can be installed either from above using the internal thread d_2 or with a socket cap screw ISO 4762 from below using the through hole d_3 . The cover cap is packaged separately and reusable.

The black version ALS offers a discreet appearance and reduces surface reflections. The version A4M is particularly suitable for use in aggressive environments.

see also...	Page
GN 338 Disks with Cover Cap (Steel, with Rubber / Plastic Cover Cap)	QVX
GN 339 Leveling Feet (Steel / Stainless Steel, with Rubber / Plastic Cover Cap)	QVX
GN 438 Spacer Disks and Foot Disks (Steel, with Vulcanized Rubber Pad)	QVX
GN 438.5 Spacer Disks and Foot Disks (Stainless Steel, with Vulcanized Rubber Pad)	QVX
GN 439 Leveling Feet (Steel, with Vulcanized Rubber Pad)	QVX
GN 439.5 Leveling Feet (Stainless Steel, with Vulcanized Rubber Pad)	QVX

How to order	
1 d_1	
2 h_1	
3 d_2	
4 Type	
5 Material	
6 Finish	

GN 440-20-30-M5-R-ALS