



2 Bore code

- B** Without keyway
- K** With keyway

1

3

d₁	d₂ H7 Bore			d₃	b	l₁	l₂ ≈
80	10	12	-	26	14	16	29
100	10	12	-	28	15	17	33
125	12	14	-	31	16	18	36
160	14	16	-	36	18	20	40
200	18	20	22	42	22	24	45
250	22	24	26	48	26	28	50
315	26	28	30	56	28	33	56
400	30	32	-	65	32	38	63

Specification

- Aluminum
 - Hub machined
 - Rim turned and polished
 - Unmachined body shot-blasted
- Radial and axial runout of the rim < 0.4
- *Keyway P9 DIN 6885 Page 1 → Page 2078*
- *Cross Holes GN 110 → Page 2080*
- *ISO Fundamental Tolerances → Page 2151*
- RoHS

Information

Disk handwheels DIN 3670 have recessed grips at their back. As a rule they are supplied without handle, but the mounting of a handle is possible.

The handwheel diameter $d_1=80$ and $d_1=400$ are not provided in the official standard sheet.

see also...

- *Countersunk Washers GN 184 (for Axial Fixing) → Page 1090*

How to order

DIN 3670- 125-K12

1	d₁
2	Bore code
3	d₂