Knurled Thumb Screws

Steel, High Type, with Internal Hex







Assembly instruction



1	2								
d_1	Length l				d_2	d_3	h	k	A/F
M 5	10	12	16	20	20	10	11,5	4	4
M 6	12	16	20	25	24	12	15	5	5
M 8	16	20	25	30	30	16	18	6	6
M 10	20	25	30	40	36	20	23	8	8

Specification

3

Steel

- Property class 8
- Head surface precision turned
- Zinc plated, blue passivated **ZB**

RoHS

Knurled thumb screws GN 464.1 have the same dimensions as specified in knurled thumb screws DIN 464. The thread of the screws generally extends up to the shoulder and ends in a runout without recess.
In comparison with DIN 464, knurled thumb screws GN 464.1 are made of a higher-quality material and additionally have an internal hex.
This makes them suitable for a wide range of applications. They can also be quickly and easily operated without tools, or, if higher torques values are required, they can be tightened or loosened with a hex socket screw key.

see also...	Page
DIN 464 Knurled Screws	QVX
DIN 653 Knurled Screws (Flat Type)	QVX
GN 653.2 Knurled Screws	QVX
GN 535 Knurled Screws (Stainless Steel)	QVX

Technical Information

Property Classes of Screws	QVX

How to order

1 2 3

GN 464.1-M8-20-ZB

1	d_1
2	Length l
3	Finish