



d <sub>1</sub>		d <sub>2</sub>	d <sub>3</sub>	h	k
Steel / Stainless Steel NI	Stainless Steel A4				
M 2	-	9	4,5	5,3	2
M 2,5	-	11	5	6,5	2,5
M 3	M 3	12	6	7,5	2,5
M 4	M 4	16	8	9,5	3,5
M 5	M 5	20	10	11,5	4
M 6	M 6	24	12	15	5
M 8	M 8	30	16	18	6
M 10	M 10	36	20	23	8
M 12	-	40	22	25	10

**Specification**

- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened
  - Zinc plated, blue passivated
- Stainless steel
  - AISI 303
  - AISI 316L
  - Matte shot-blasted
- *Strength Values of Nuts* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS



**Information**

Knurled nuts DIN 466 are suitable for universal use and can be tightened and loosened easily without tools. A nut with thread M12 is also available in addition to the types defined in the DIN standard.

see also...

- *Knurled Nuts GN 536 (Stainless Steel)* → Page 640
- *Knurled Nuts DIN 6303 (Stainless Steel)* → Page 643
- *Knurled Nuts DIN 467 (Flat Type)* → Page 648
- *Knurled Nuts DIN 466 (with Loss Protection GN 111.7)* → Page 2084

How to order (Steel, blackened)

**DIN 466-M6** 1 d<sub>1</sub>

How to order (Steel, zinc plated)

**DIN 466-M10-ZB** 1 d<sub>1</sub>  
2 Finish

How to order (Stainless steel)

**DIN 466-M2-NI** 1 d<sub>1</sub>  
2 Material