



4 Type
C With fastening set



1 l_1	2 n_1	3 n_2	d_1	d_2	l_2	l_3	m_1	m_2	A/F_1	A/F_2
24	6	6	M 6	M 6	27	27	15	15	4	4
32	8	8	M 8	M 8	36	36	20	20	5	5

Specification

- Housing
Zinc Die Casting
Painted, white aluminum **ZW**
- Fastening set
Screws, T-nuts and bushing
Steel, zinc plated, blue passivated **SZ**
- RoHS

Information

Rotating angle brackets GN 41i connect two intersecting aluminum profiles, rotatably mounted via a bushing. Machining of the profile is not necessary.

see also...

- Aluminum Profiles GN 10i (Profile Type Light) → Page QVX
- Aluminum Profiles GN 10i (Profile Type Heavy) → Page QVX
- Aluminum Profiles GN 11i (with Partially Closed Slots) → Page QVX

How to order

1	l_1
2	n_1
3	n_2
4	Type
5	Finish (Housing)
6	Material / Finish (Fastening set)

GN 41i-3288-C-ZWSZ

