



ROSTFREI
Inox
Stainless
Steel

2

3

d ₁		Length l ±0,25			d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	r	s max.
Stainless steel	Steel											
6	-	55*	64	88*	M 6	12	21	27,5	9,5	10	6	4
10	10	100	120	180	M 10 x 1	18	34	43	14	14	12	6

* Suitable for 19" rack and enclosure layout

Specification

1

4

- Steel **ST**
Chrome-plated **CR**
- Stainless steel AISI 303 **NI**
Matte shot-blasted **GS**
- Hexagon nuts ISO 8675
Stainless steel AISI 304
- Location disks DIN 125
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Folding handles GN 425.2 are used in such applications where minimal protrusion is required.

In both positions the handle is retained by a spring loaded detent.

see also...

- *Folding Handles with Recessed Tray GN 425.8 (with Handle Locking or Spring-Loaded Return)* → Page 176
- *Folding Handles GN 425.9 (Stainless Steel, with / without Retaining Spring)* → Page 174
- *Folding Handles GN 825.1 (Plastic, with Spring-Loaded Return)* → Page 175

How to order

GN 425.2-NI-10-180-GS

- 1 Material
- 2 d₁
- 3 Length l
- 4 Finish