



3 Type

- F With fixed handle
- D With revolving handle

Length l	1 s H11 Square		e min. (Column 1)	2 (Column 2)	d ₁ H7 Bore	d ₂	h ₁	h ₂	h ₃ ≈	h ₄ ≈		Ø Handle
	Type D	Type F										
63	V 10	-	13,1	-	-	20	20	11	32	54,5	50	16
80	V 10	V 12	13,1	16,1	B 8	24	24	13	38	61	56	18
100	V 12	V 14	16,1	18,1	B 10	28	28	13	48	67	64	20
125	V 14	V 17	18,1	22,2	B 10	34	34	14	55	76	72	22
160	V 17	V 19	22,2	25,2	B 14	38	38	14	65	83	80	25
200	V 19	V 22	25,2	28,2	B 17	44	44	21	78	96,5	90	28
250	V 22	V 24	28,2	32,2	B 17	48	48	21	90	105,5	100	32
315	V 24	V 27	32,2	36,2	B 20	54	54	26	105	117	112	36

Specification

- Body
Cast iron (GGG)
 - Powder coated
Black, textured finish
 - Face of the hub machined
- Fixed handles DIN 39
Steel zinc plated, blue passivated
- Revolving handles DIN 98
Steel zinc plated, blue passivated
- Squares DIN 79 → Page 2082
- Cross Holes GN 110 → Page 2080
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

The hub bores d₁ H7 are not provided for in the official standard sheet.

How to order

DIN 468-100-V14-F

- 1 Length l
- 2 s (d₁)
- 3 Type