


Application and mounting example



d <sub>1</sub>	Length l ±0,5			d <sub>2</sub> H12	h	r	t
	64	88	100				
8	64	88	100	3	35	10	5
10	100	125	160	3	43	12	5
12	125	160	200	4	51	14	6
16	125	160	200	4	59	18	6
20	200	250	-	5	68	22	8

Specification

<b>Steel</b>	<b>ST</b>
Matte, shot blasted	
<b>Stainless steel AISI 304</b>	<b>NI</b>
Matte, shot blasted	
RoHS	

Cabinet U-handles GN 425.3 are made of bent steel or stainless steel sections and are affixed by welding.

The holes d<sub>2</sub> serve, if necessary, for inserting dowel pins or guide pins that provide a simple method for positioning and fixing the cabinet U-handle in place via the alignment holes in the opposing part for the welding process.

see also...

	Page
GN 426.3 Cabinet U-Handles (Steel, for Welding)	QVX
GN 425 Cabinet U-Handles (Steel, Aluminum, Stainless Steel)	QVX
GN 426 Cabinet U-Handles (Aluminum)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN 425.3-8-64-ST

1	d <sub>1</sub>
2	Length l
3	Material

