Cranked Handles

Steel, Forged / Cast Iron





3 Type

F With fixed handle
D With revolving handle

1 Length l	2 s H11 Square		e min. (Column 1)	(Column 2)	2 d_1 H7 Bore	d_2	h_1	h_2	h_3 ≈	h_4 ≈ Type D	Type F	Ø Handle
63	V 10	-	13,1	-	-	20	20	11	15	54,5	50	16
80	V 10	V 12	13,1	16,1	B 8	24	24	13	18	61	56	18
100	V 12	V 14	16,1	18,1	B 10	28	28	13	21	67	64	20
125	V 14	V 17	18,1	22,2	B 10	34	34	14	26	76	72	22
160	V 17	V 19	22,2	25,2	B 14	38	38	14	29	83	80	25
200	V 19	V 22	25,2	28,2	B 17	44	44	21	34	96,5	90	28
250	V 22	V 24	28,2	32,2	B 17	48	48	21	36	105,5	100	32

Specification

Body
Forged steel / Cast iron (GGG)
- Powder coated
  Black, textured finish
- Face of the hub machined

Fixed handle DIN 39 for type F
Steel
Zinc plated, blue passivated

Revolving handle DIN 98 for type D
Steel
Zinc plated, blue passivated

RoHS

The hub bores d_1 H7 are not provided for in the official standard sheet.

see also...	Page
DIN 468 Cranked Handles (cranked)	QVX

Technical Information

Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX

How to order

DIN 469-125-V17-D (1 2 3)

1	Length l
2	s (d_1)
3	Type