



3 Type

- F With fixed handle
- D With revolving handle

Length l	1 s H11		2 e min.		d ₁ H7 Bore	d ₂	h ₁	h ₂	h ₃ ≈	h ₄ ≈		Ø Handle
	Square		(Column 1)	(Column 2)						Type D	Type F	
63	V 10	-	13,1	-	-	20	20	11	15	54,5	50	16
80	V 10	V 12	13,1	16,1	B 8	24	24	13	18	61	56	18
100	V 12	V 14	16,1	18,1	B 10	28	28	13	21	67	64	20
125	V 14	V 17	18,1	22,2	B 10	34	34	14	26	76	72	22
160	V 17	V 19	22,2	25,2	B 14	38	38	14	29	83	80	25
200	V 19	V 22	25,2	28,2	B 17	44	44	21	34	96,5	90	28
250	V 22	V 24	28,2	32,2	B 17	48	48	21	36	105,5	100	32

Specification

Body

Cast iron (GGG)

- Powder coated
- Black, textured finish
- Face of the hub machined

Fixed Handle DIN 39 for type F

Steel

Zinc plated, blue passivated

Revolving Handle DIN 98 for type D

Steel

Zinc plated, blue passivated

RoHS

The hub bores d₁ H7 are not provided for in the official standard sheet.

see also...

DIN 468 Cranked Handles (cranked)

Page

QVX

Technical Information

Cross holes GN 110

QVX

Squares DIN 79

QVX

ISO Fundamental Tolerances

QVX

How to order

DIN 469-125-V17-D

- 1 Length l
- 2 s (d₁)
- 3 Type