



**3 Type**

- A** Mounting from the back with thread
- B** Mounting the operator's side with through hole
- C** Mounting from the operator's side by welding

**4 Identification no.**

- 1** Handle 90° foldaway
- 2** Handle 90° foldaway, with retaining springs
- 3** Handle 180° foldaway
- 4** Handle 180° foldaway, with retaining springs

**1**

Length l	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub>	h <sub>4</sub>	m	t <sub>1</sub>	t <sub>2</sub>
120	124	20	106	M 6	6,4	16	53	49	59	60	10	9,6

**Specification**

**2** **5**

**Attachment part**

Stainless steel		
precision casting AISI CF-8	<b>NI</b>	
• Matte shot-blasted finish		<b>GS</b>
• Powder coated		
Black, RAL 9005, textured finish only in type A and B	<b>● SW</b>	

**Handle bar**

Stainless steel AISI 304  
Matte shot-blasted

**Retaining springs**

Spring steel AISI 301

RoHS

Folding handles GN 425.9 are used where the handle must only protrude a short distance in the resting position.

Folding handles numbers 1 and 2 are suitable for side "access," as these have a 90° limit stop. If used from above, numbers 3 and 4 with a handle which can fold freely through 180° are a better version.

The retaining springs of numbers 2 and 4 keep the handle in any position. This keeps the handle in a position which can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

**see also...**

<b>GN 425.8</b> Folding Handles with Recessed Tray (Steel / Stainless Steel, with Handle Locking or Spring-Loaded Return)	<b>Page</b> QVX
--	--------------------

**Technical Information**

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

**How to order**

<b>1</b>	Length l
<b>2</b>	Material
<b>3</b>	Type
<b>4</b>	Identification no.
<b>5</b>	Finish

**GN 425.9-120-NI-A-1-SW**