


0 resp. arrow opposite grub screw



3 Type

- A** With arrow
- B** Neutral, without arrow or scale
- S** With standard scale 0...9, 20 graduations



1 d_1	2 d_2 H8 Bore		d_3	d_4	h_1	h_2	Length l	t min.
24	B 5	B 6	22	M 4	24	8	12	18
28	B 6	B 8	26	M 4	27	9	13	20

Specification

Knob

- Stainless steel AISI 304
- Matte shot-blasted finish
- Arrow for type A
- Laser-engraved
- Scale for type S
- Laser-engraved

MT

Grub screw DIN 916

Stainless steel
with internal hex and with serrated point

RoHS

On request

- Special graduations (see „How to Order Graduations“)

Scale and arrow on the Stainless Steel-control knobs GN 436.1 are indelibly marked and easily legible.

Besides the standard scale (Type S) the control knobs can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to order Graduations“

see also...

GN 436 Control Knobs	Page QVX
-----------------------------	--------------------

Technical Information

How to order - Graduations	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

1 d_1
2 d_2
3 Type
4 Finish

GN 436.1-28-B6-S-MT