




elesa
Original design THR-RC / THR-LP

- 3

Identification no.
- 1 Without vent hole
- 5 Type
- R With retaining ring
- P With plastic ball chain

<div>1</div> <div>d₁</div>	<div>2</div> <div>d₂</div>	<div>3</div> <div>l₁</div>	<div>4</div> <div>l₂</div>	<div>5</div> <div>r</div>	<div>6</div> <div>s</div>
32	G 1/2	29	11	26	4
37	G 3/4	32,5	12	28,5	5
44	G 1	36	13	32	6

Specification

Threaded plug

Plastic, polyamide (PA)
Black, matte finish

● B

O-Ring

Acrylonitrile butadiene rubber (NBR)

Retaining ring / Ball chain

Plastic, polyacetal (POM)
Black

Key ring on type P

Stainless steel AISI 301
Chemically blackened

Operating temperature 0 °C to +60 °C

RoHS

Accessory [ganternorm.com](https://www.ganternorm.com)

- GN 111.3 Key Rings (Stainless Steel)
- GN 111 Ball Chains (Brass)
- GN 111.5 Ball Chains (Stainless Steel)
- GN 111.2 Retaining Cables (Stainless Steel)
- GN 111.8 Retaining Cables (Stainless Steel Quality Class 4)
- GN 111.4 Spiral Retaining Cables (Plastic)
- GN 7490 Welding Sockets (Steel / Stainless Steel)

Threaded plugs GN 443.13 with the external diameter d₁ match the screw-in holes for DIN 3852 pipe fittings.

The O-ring is embedded in a radial groove on the flat side. This protects against loss and prevents it from being squeezed out during tightening.

The affixed retaining ring allows threaded plugs GN 443.13 to be secured with a ball chain or retaining cable to prevent loss.

Type P is delivered with attached retaining ring and ball chain.

see also... [ganternorm.com](https://www.ganternorm.com)

GN 443 Threaded Plugs (Plastic)

GN 741 | GN 742 Threaded Plugs (with External Hex)

GN 548.1 Plugs (Plastic)

Technical Information

Plastic Characteristics

Stainless Steel Characteristics

How to order		1	d ₁
		2	d ₂
		3	Identification no.
		4	Color
		5	Type
GN 443.13-37-G3/4-1-B-P			