


Clamping kit GN 511



| 1 d₁ Bore for shaft tol. h11 | 2 d₂ Bore for shaft tol. h11 | d₃ Claming thread | d₄ Claming thread | k₁ | k₂ | l₁ | l₂ | l₃ | m | s₁ Square | s₂ Square | Clamping kits | |
|--|--|--|--|----------------------|----------------------|----------------------|----------------------|----------------------|----------|--------------------------------|--------------------------------|--------------------------|--------------------------|
| | | | | | | | | | | | | for d₃ | for d₄ |
| B 8 | B 8 | M 4 | M 4 | 16 | 16 | 52,5 | 13 | 13 | 26,5 | - | - | GN 511-M4-16 | GN 511-M4-16 |
| B 10 | B 8 | M 5 | M 4 | 20 | 16 | 58 | 15,5 | 13 | 29,5 | 8 | - | GN 511-M5-20 | GN 511-M4-16 |
| B 10 | B 10 | M 5 | M 5 | 20 | 20 | 63,5 | 15,5 | 15,5 | 32,5 | 8 | 8 | GN 511-M5-20 | GN 511-M5-20 |
| B 12 | B 8 | M 5 | M 4 | 20 | 16 | 62 | 16,5 | 13 | 32,5 | 10 | - | GN 511-M5-20 | GN 511-M4-16 |
| B 12 | B 12 | M 5 | M 5 | 20 | 20 | 71,5 | 16,5 | 16,5 | 38,5 | 10 | 10 | GN 511-M5-20 | GN 511-M5-20 |
| B 15 | B 10 | M 6 | M 5 | 25 | 20 | 75,5 | 20 | 15,5 | 40 | 12 | 8 | GN 511-M6-25 | GN 511-M5-20 |
| B 15 | B 12 | M 6 | M 5 | 25 | 20 | 79,5 | 20 | 16,5 | 43 | 12 | 10 | GN 511-M6-25 | GN 511-M5-20 |
| B 15 | B 15 | M 6 | M 6 | 25 | 25 | 87,5 | 20 | 20 | 47,5 | 12 | 12 | GN 511-M6-25 | GN 511-M6-25 |
| B 16 | B 12 | M 6 | M 5 | 25 | 20 | 81 | 20 | 16,5 | 44,5 | - | 10 | GN 511-M6-25 | GN 511-M5-20 |
| B 16 | B 16 | M 6 | M 6 | 25 | 25 | 90,5 | 20 | 20 | 50,5 | - | - | GN 511-M6-25 | GN 511-M6-25 |
| B 20 | B 15 | M 6 | M 6 | 30 | 25 | 95 | 22 | 20 | 53 | 16 | 12 | GN 511-M6-30 | GN 511-M6-25 |
| B 20 | B 16 | M 6 | M 6 | 30 | 25 | 96,5 | 22 | 20 | 54,5 | 16 | - | GN 511-M6-30 | GN 511-M6-25 |
| B 20 | B 20 | M 6 | M 6 | 30 | 30 | 102,5 | 22 | 22 | 58,5 | 16 | 16 | GN 511-M6-30 | GN 511-M6-30 |

Specification

- Aluminum
 - Matte finish, tumbled **MT**
 - Black anodized **ELS**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Grub screw DIN 915
Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Clamping Kits GN 511 → Page 1804

Information

Twistable two-way mounting clamps GN 475 connect rods and tubes within the mounting clamp system under any adjustable angle. With the angle adjustment released, the mounting clamp halves stay connected with formlocking effect.

In the standard version, the clamping screws at the clamping threads **d₃** and **d₄** are a socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 511 (article code see table of dimensions).

see also...

- Retaining Rods / Retaining Tubes GN 480.1 → Page 1833
- Twistable Two-Way Clamp Mountings GN 490 → Page 1774

How to order

GN 475-B10-B10-MT

- 1 **d₁**
- 2 **d₂**
- 3 **Finish**