





Assembly instruction



- 4

Type
- A Without rubber pad
- AG With rubber pad

1 d₁	2 d₂	3 l₁				b	d ₃	k ₁	k ₂	l ₂	l ₃	l ₄	A/F ₁	A/F ₂	Ball Ø	Static load in kN (see information)
60	M 8	44	69	-		96,5	8,5	50	18	31,5	14	21	16	3	14	2,7
60	M 10	44	69	99		96,5	8,5	50	18	31,5	14	21	16	4	14	4,8
60	M 12	44	69	99		96,5	8,5	50	18	31,5	14	21	16	5	14	6,8
80	M 8	44	69	-		130	10,5	70	25	33	14	22	16	3	14	2,7
80	M 10	44	69	99		130	10,5	70	25	33	14	22	16	4	14	4,8
80	M 12	44	69	99		130	10,5	70	25	33	14	22	16	5	14	6,8

Specification

Base plate

Plastic, polyamide (PA)

• Glass fiber reinforced

• Black, matte finish

Threaded stud

Plastic, polyamide (PA-HP)

• Glass fiber reinforced

• Black, matte finish

Rubber pad for type AG

Acrylonitrile butadiene rubber (NBR)

Hardness 70 Shore A, black

Operating temperature

-30 °C to +100 °C

RoHS

Technical Information

Plastic Characteristics

Page

QVX

Leveling feet GN 445.9 are made of plastic, making them lightweight, resistant to corrosion and electrically insulating. They are used for setting up and leveling machines, devices and equipment.

The geometry of the base plate distributes the load over a large area and, in combination with the high-quality plastic, results in a high static load capacity.

The leveling feet are supplied assembled, but they can also be taken apart. The mounting holes in the base plate are sealed with a thin layer of plastic when delivered, which can be easily pierced or drilled through.

The static load capacity values specified in the table are non-binding guidelines; exceeding these values may result in deformation or component failure.

see also...

GN 445 Leveling Feet (Plastic, Threaded Stud Steel)

QVX

GN 445.5 Leveling Feet (Plastic, Threaded Stud Stainless Steel)

QVX

How to order

1

d₁

2

d₂

3

l₁

4

Type

GN 445.9-60-M12-99-A