



¹ d ₁ Bore for shaft tol. h11	² d ₂			d ₃ Clamping thread	k	l ₁	l ₂	l ₃	m	s Square	t	Clamping lever for d ₃
B 8	M 5	-	-	M 4	14	25	13,5	11,5	-	-	7,5	GN 511-M4-14
B 10	M 5	M 6	M 8	M 5	16	30	17	13	-	8	8	GN 511-M5-16
B 12	M 5	M 6	M 8	M 5	16	32	17	15	-	10	9	GN 511-M5-16
B 15	M 6	M 8	-	M 6	20	40	20,5	19,5	14	12	12	GN 511-M6-20
B 16	M 6	M 8	-	M 6	20	40	20,5	19,5	14	-	11,5	GN 511-M6-20
B 20	M 8	M 10	-	M 6	25	45	21,5	23,5	17	16	12	GN 511-M6-25

Specification

Mounting clamp

- Aluminum
- Matte, ground
- Anodized, black



MT
ELS

Socket cap screws ISO 4762

Stainless steel

RoHS

Attachment mounting clamps GN 478 are primarily designed for mounting sensor holders GN 479 and retaining plates GN 479.1. They are fitted with a central thread and, with d₁ = B15 bore and higher, an additional bore template 4 x M4.

In the standard version the clamping screw is a socket cap screw with hexagonal socket ISO 4762. It can be replaced by a clamping kit GN 511 (article code see table of dimensions).

see also...	Page
GN 479 Sensor Holders (Stainless Steel)	QVX
GN 479.1 Retaining Plates (Stainless Steel)	QVX

Technical Information

Range	QVX
Application examples clamp mountings	QVX
ISO Fundamental Tolerances	QVX

Accessory

GN 511 Clamping Kits	QVX
GN 480.1 Retaining Rods / Retaining Tubes	QVX

How to order

GN 478-B16-M6-ELS

¹	d ₁
²	d ₂
³	Finish