



<div>1</div> <div>d<sub>1</sub> h9</div>	<div>2</div> <div>l<sub>1</sub></div>		b	d <sub>2</sub>	d <sub>3</sub> For screw	l <sub>2</sub>	l <sub>3</sub>	m
8	18	32	14	31,5	M 4	6	2	22
10	21	37	16	38	M 5	8	2,5	27
12	22	39	16	38	M 5	8	2,5	27
15	27,5	47,5	20	45	M 6	10	4	32
16	28	49	20	45	M 6	10	4	32
20	35	60	25	50	M 6	10	4	36

Specification

- Steel  
Zinc plated, blue passivated
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

Flange mounting bolts GN 480 are used with mountings clamps or for attachment to profile systems, as base plate or connecting element, e.g. for adjusting the width or height.

With their low flange height, they provide an alternative for the base plate mounting clamps GN 473 in applications where clamping is required at low height above the clamping surface.

The bore distance m corresponds to base plate mounting clamps GN 473, mounting clamps GN 477, base plate swivel mounting clamps GN 485, as well as retaining magnets GN 51.6.

- see also...
- Product Family Standard Parts for Profile Systems → Page 18
  - Assembly Sets for Profile Systems 30 / 40 GN 965 → Page 2086
  - Assembly Sets for Profile Systems 30 / 40 / 45 GN 968 → Page 2096

How to order	1	d <sub>1</sub>
	2	l <sub>1</sub>
GN 480-12-39		