



d <sub>1</sub>		Length l								d <sub>2</sub>	d <sub>3</sub>	h	k
Steel / Stainless steel NI	Stainless steel A4	4	6	8	10	-	-	-	-				
M 2	-	4	6	8	10	-	-	-	-	9	4,5	5,3	2
M 2,5	-	4	6	8	10	12	-	-	-	11	5	6,5	2,5
M 3	M 3	6	8	10	12	16	20	-	-	12	6	7,5	2,5
M 4	M 4	5	8	10	12	16	20	25	-	16	8	9,5	3,5
M 5	M 5	6	8	10	12	16	20	25	30	20	10	11,5	4
M 6	M 6	8	10	12	16	20	25	30	35	24	12	15	5
M 8	M 8	12	16	20	25	30	35	40	-	30	16	18	6
M 10	-	12	15	20	25	30	35	40	-	36	20	23	8

**Specification**

- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened
  - Zinc plated, blue passivated
- Stainless steel
  - AISI 303
  - AISI 316L
  - Matte shot-blasted
- *Strength Values of Screws* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Knurled screws DIN 464 are turned entirely from a single piece. The thread of the screw generally extends up to the shoulder and ends in a runout without recess.

They are suitable for universal use and can be quickly tightened and loosened without tools.

see also...

- *Knurled Screws DIN 653 (Flat Type)* → Page 649
- *Knurled Screws GN 653.2 (with Recessed Stud for Loss Protection)* → Page 651
- *Knurled Screws GN 535 (Stainless Steel)* → Page 640
- *Knurled Screws DIN 464 (with Loss Protection GN 111.7)* → Page 2084

How to order (Steel, blackened)	1	d <sub>1</sub>
<b>DIN 464-M6-20</b>	2	Length l

How to order (Steel, zinc plated)	1	d <sub>1</sub>
<b>DIN 464-M2,5-6-ZB</b>	2	Length l
	3	Finish

How to order (Stainless steel)	1	d <sub>1</sub>
<b>DIN 464-M10-35-NI</b>	2	Length l
	3	Material