




1 2 3											d ₂	h ₁	h ₂	h ₃	h ₄ Stroke
l ₁	d ₁	l ₂													
42	M 5	10	16	20	-	-	-	-	-	-	12	27	6	32	3,5
42	M 6	10	16	20	25	30	40	-	-	-	12	27	6	32	3,5
63	M 6	10	16	20	25	30	35	40	-	-	15	34	8	43	4
63	M 8	16	20	25	30	35	40	45	50	60	15	34	8	43	4
80	M 10	20	25	30	35	40	50	60	70	-	19	42	10	54	4
80	M 12	20	25	30	35	40	50	60	70	80	19	42	10	54	4
100	M 12	30	50	70	-	-	-	-	-	-	25	48	12	65	5
100	M 14	30	50	-	-	-	-	-	-	-	25	48	12	65	5
100	M 16	30	50	70	-	-	-	-	-	-	25	48	12	65	5

Specification

4

Handle

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -30 °C to +120 °C
- Black, RAL 9005, matte finish

Releasing button

Plastic, black

Insert

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Black
- Threaded stud
 - Steel zinc plated, blue passivated

RoHS

On request

- with threaded stud in stainless steel
- Other colors

Adjustable hand levers GN 503 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged. Pulling the lever, disengages the serrations and allowing it to be swiveled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

Its use is, however, limited to applications where dismantling of the lever for installation is not required. The threaded insert can after disengagement be screwed in using the serration of the insert.

Technical Information	Page
Plastic Characteristics	QVX

How to order

1

2

3

4

GN 503-63-M8-20-SW

1	l ₁
2	d ₁
3	l ₂
4	Color

2.1 Tensioning, Clamping, Switching with Levers

1