



1.1

1.2

1.3

1.4

¹ d ₁	² d ₂ Thread	² d ₃ H9 Bore	b	d ₄	h ₁	h ₂ ≈	t min.
63	M 6	B 6	7	16	41	12	12
63	M 8	B 8	7	16	41	12	16
80	M 8	B 8	9	21	52	15	16
80	M 10	B 10	9	21	52	15	20
100	M 10	B 10	11	25	65	19	20
100	M 12	B 12	11	25	65	19	24

Specification

- Stainless steel AISI 316
- Matte shot-blasted finish
- Polished finish
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

³

MT
PL

Information

T-handles GN 5063 are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the materials used.

see also...

- T-Handles GN 5064 (Stainless Steel, Hygienic Design) → Page XYZ
- T-Handles GN 563 (Plastic) → Page 92
- T-Handle Screws GN 563.1 (Plastic) → Page 93
- T-Handles GN 563.2 (Aluminum) → Page 91
- Wing Nuts GN 8340 (Stainless Steel) → Page XYZ
- Wing Screws GN 8350 (Stainless Steel) → Page XYZ

2.1

2.2

2.3

2.4

How to order	1
¹ d ₁	d ₁
² d ₂ (d ₃)	d ₂ (d ₃)
³ Finish	Finish

GN 5063-80-M10-MT