



1

d ₁	d ₂	d ₃	h	k
M 3	12	6	3	2,5
M 4	16	8	4	3,5
M 5	20	10	5	4
M 6	24	12	6	5
M 8	30	16	8	6
M 10	36	20	10	8
M 12	40	22	12	10

Specification

- Steel
 - Property class 5
 - Visible face fine turned
 - Blackened —
 - Zinc plated, blue passivated **ZB**
- Stainless steel AISI 303 **NI**
Matte shot-blasted
- *Strength Values of Nuts* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Version in stainless steel (A4 quality)

2

Information

Knurled nuts DIN 467 are suitable for universal use and can be tightened and loosened easily without tools. A nut with thread M12 is also available in addition to the types defined in the DIN standard.

see also...

- *Knurled Nuts GN 536 (Stainless Steel)* → Page 640
- *Knurled Nuts DIN 6303* → Page 643
- *Knurled Nuts DIN 466 (High Type)* → Page 646
- *Knurled Nuts DIN 466 (with Loss Protection GN 111.7)* → Page 2084

How to order (Steel, blackened)

DIN 467-M3 1 d₁

How to order (Steel, zinc plated)

DIN 467-M12-ZB 1 d₁
2 Finish

How to order (Stainless steel)

DIN 467-M8-NI 1 d₁
2 Material