



¹ d ₁	² d ₂ Thread	² d ₃ H9 Bore	b	d ₄	h ₁	h ₂ ≈	t min.
63	M 6	B 6	7	16	41	12	12
63	M 8	B 8	7	16	41	12	16
80	M 8	B 8	9	21	52	15	16
80	M 10	B 10	9	21	52	15	20
100	M 10	B 10	11	25	65	19	20
100	M 12	B 12	11	25	65	19	24

Specification

- Stainless steel AISI 316
- Matte shot-blasted finish
- Polished



MT
PL

RoHS

T-handles GN 5063 are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the materials used.

see also...

	Page
GN 563 T-Handles (Plastic)	QVX
GN 563.1 T-Handle Screws (Plastic)	QVX
GN 563.2 T-Handles (Aluminum)	QVX
GN 8340 Wing Nuts	QVX
GN 8350 Wing Screws	QVX
GN 5064 T-Handles	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN 5063-80-M10-MT

¹ d ₁	
² d ₂ (d ₃)	
³ Finish	