



1

2

a _{-0,3 -0,5}	d			e	h	k	For T-slots DIN 650
5	M 4	-	-	9 -0,5	6,5	3 -0,3	5
6	M 5	-	-	10 -0,5	8	4 -0,5	6
8	M 6	-	-	13 -0,5	10	6 -0,5	8
10	M 6	M 8	-	15 -0,5	12	6 -0,5	10
12	M 8	M 10	-	18 -0,5	14	7 -0,5	12
14	M 10	M 12	-	22 -0,5	16	8 -0,5	14
16	M 10	M 12	M 14	25 -0,5	18	9 -0,5	16
18	M 12	M 14	M 16	28 -0,5	20	10 -0,5	18
20	M 12	M 16	M 18	32 -0,5	24	12 -0,5	20
22	M 16	M 20	-	35 -0,5	28	14 -0,5	22
24	M 20	M 22	-	40 -0,5	32	16 -0,5	24
28	M 20	M 24	-	44 -1	36	18 -1	28
36*	M 30	-	-	54 -1	44	22 -1	36
42*	M 36	-	-	65 -1	52	26 -1	42

* not available from stock in property class 8, requires a minimum order quantity

Specification

- Heat-treated steel
- Property class **8**
Plain
- Property class **10**
Blackened
- *Strength Values of Nuts* → Page 2152
- RoHS

3

Information

T-nuts DIN 508 with the property class 8 (plain) are also available without thread. They can be adapted for special applications in this way.

see also...

- *T-Nuts GN 508.2 (with Slip Proof)* → Page 1164
- *Studs DIN 6379* → Page 1166

How to order (With thread)

DIN 508-14-M12-8

- 1 a
- 2 d
- 3 Property class

How to order (Without thread)

DIN 508-20-8

- 1 a
- 3 Property class