



1.1

1.2

1.3

1.4

Length l	d ₁ H7 Bore	s H11 Square	d ₂	d ₃	h ₁	h ₂ ≈	h ₃	h ₄	h ₅ ≈	Ø Handle
80	B 10	V 10	23	30	19,5	4	25,5	4,3	43	16
100	B 12	V 12	26,7	35	23,5	5,5	29,5	4,2	57,5	18
125	B 14	V 14	28	37	30,5	10,5	36,5	4,2	76,5	24

Specification

- Body
Aluminum
 - Powder coated
Black, RAL 9005, textured finish ● **SW**
 - Silver, RAL 9006, textured finish ● **SR**
 - Contact face of hub machined
- Hub cover
Plastic
Light gray
- Retractable handles GN 798.3
 - Plastic, Technopolymer
Black, matte finish
 - Retractable mechanism
Steel, blackened
- Retractable handles GN 798.5
 - Plastic, Technopolymer
Black, matte finish
 - Retractable mechanism stainless steel
 - Axle parts AISI 303
 - Flat base
Sintered steel AISI 316
- Cross Holes GN 110 → Page 2080
- Squares DIN 79 → Page 2082
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

The handle of the cranked handles with retractable handle GN 472.3 / GN 472.5 is locked in a tapered bore in the operating position.

For tilting, the handle must first be pulled out of the taper in axial direction.

A pressure spring holds the handle in both end positions. When folded out, it automatically re-engages.

2.1

2.2

2.3

2.4

How to order (Retractable mechanism steel)

GN 472.3-100-V12-SR

1	Length l
2	s (d ₁)
3	Color

How to order (Retractable mechanism stainless steel)

GN 472.5-125-B14-SW

1	Length l
2	d ₁ (s)
3	Color