



1 2 3

l ₁	d ₁	l ₂		d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke							
42	M 5	10	16	20	-	-	-	-	-	-	12	18	16	27	6	32	3,5
42	M 6	10	16	20	25	30	40	-	-	-	12	18	16	27	6	32	3,5
63	M 6	10	16	20	25	30	40	-	-	-	15	23	20	34	8	43	4
63	M 8	16	20	25	30	35	40	45	50	60	15	23	20	34	8	43	4
80	M 10	20	25	30	35	40	50	60	70	-	19	28	24	42	10	54	4
80	M 12	20	25	30	35	40	50	60	70	80	19	28	24	42	10	54	4
100	M 12	30	50	70	-	-	-	-	-	-	25	33	31	48	12	65	5
100	M 16	30	50	70	-	-	-	-	-	-	25	33	31	48	12	65	5

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black, RAL 9005, matte finish **SW**
- Threaded stud and retaining screw
Steel, blackened
- *Plastic Characteristics* → Page 2158
- RoHS

On request

- Other colors

4

Information

Adjustable hand levers GN 500 besides their good design, offer the advantage that the plastic material used is fully penetrated by the colour and will not show any discolouring through abrasion or use.

When pulling the handle, the serration frees itself and can be re-located into any required position. When „releasing“ the lever the serration re-engages automatically.

see also...

- *Adjustable Hand Levers GN 503 (with Releasing Button)* → Page 479

How to order

1	l ₁
2	d ₁
3	l ₂
4	Color

GN 500-80-M10-40-SW

