



¹ a $\begin{smallmatrix} -0,3 \\ -0,5 \end{smallmatrix}$	² d	e -0,5	h	k -0,5	For T-slots DIN 650
8	M 6	13	10	6	8
10	M 8	15	12	6	10
12	M 10	18	14	7	12
14	M 12	22	16	8	14
16	M 14	25	18	9	16
18	M 16	28	20	10	18
22	M 20	35	28	14	22

Specification

- Heat-treated steel
 - Property class 10
 - Blackened
- *Strength Values of Nuts* → Page 2152
- RoHS

Information

Rhombus T-nuts GN 508.1 can be inserted vertically into the T-slot.
 see also...
 • *T-Nuts DIN 508* → Page 1162

How to order GN 508.1-14-M12	¹ a
	² d

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

