



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	b	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	t min.
63	M 6	7	16	16,8	12	41	12	12
80	M 8	9	21	21,8	17	52	15	16
100	M 10	11	25	25,8	21	65	19	20

**Specification**

- Handle**  
Stainless steel precision casting AISI 316
  - Matte finish (Ra < 0.8 µm) **MT**
  - Polished finish (Ra < 0.8 µm) **PL**
- Sealing ring**
  - H-NBR **H**
  - EPDM **E**
  - Operating temperature -25 °C to + 150 °C
  - Operating temperature -40 °C to + 120 °C
  - Blue
  - Hardness 85±5 Shore A
  - FDA compliant

RoHS

**On request**

- with FKM sealing ring (Fluorine rubber) **F**

T-handles GN 5064 comply with the DGVU testing principles and are intended for use in hygienic areas. The version with PL finish is additionally certified according to the guidelines of the EHEDG. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

T-handles are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the material used.

**see also...**

	Page
GN 563.2 T-Handles (Aluminum)	QVX
GN 5063 T-Handles (Stainless Steel)	QVX
GN 8341 Wing Nuts (Stainless Steel, Hygienic Design)	QVX
GN 563 T-Handles (Plastic)	QVX
GN 563.1 T-Handle Screws (Plastic)	QVX

**Technical Information**

Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	
<sup>1</sup> d <sub>1</sub>	
<sup>2</sup> d <sub>2</sub>	
<sup>3</sup> Finish	
<sup>4</sup> Material (Sealing ring)	

**GN 5064-63-M6-PL-E**