
GN 515

Latches

Zinc Die Casting, with Extended Housing, with Operating Elements





 Lock housing Zinc die casting Housing collar

Black, RAL 9005, textured finish

Powder coated

· Operating elements

Black, matte finish

Plastic (Polyamide PA)

Plastic (Polyamide PA)

Light gray, matte finish

· Cover cap (Type RG, KG, HG)

Steel, zinc plated, blue passivated

ZD

SW

Latches GN 515 are identical to standard latches GN 115 except for the extended housing. They are operated with a rotation limited to 90°, which moves the latch arm into the locked position behind the frame. The bevels of the latch arm ease the closing of the door.

By installing latch arms with different bend profiles, the latch distance A can be varied from 16 to 92 mm depending on the housing height h₁, while the extended housing is suitable for a door thickness s up to 50 mm.

Latches GN 515 are supplied with loosely enclosed latch arm.

see also ...

Construction and Assembly Instructions → Page XYZ

How to order	1	Material	
₽ ₽ ₽ ₽ GN 515-ZD-RG-60-55-SW	2	Туре	5
	3	h ₁	
	4	Latch arm distance A	
	5	Finish	

- Protection class IP65 IP Protection Classes → Page QVX
- RoHS

· Other parts

Page 1

00

ő

O

ന്