



ROSTFREI
Inox
Stainless
Steel

3.1

3.2

3.3

3.4

1

2

a ^{-0,3 -0,5}	d	e ^{-0,5}	h	k ^{-0,5}	For T-slots DIN 650
8	M 6	13	10	6	8
10	M 8	15	12	6	10
12	M 10	18	14	7	12
14	M 12	22	16	8	14
16	M 14	25	18	9	16
18	M 16	28	20	10	18

3.5

3.6

Specification

- Stainless steel
- AISI 316LHC (with thread)
- AISI 304 (without thread)
- *Stainless Steel Characteristics* → Page 2166
- RoHS

3

NI

Information

Stainless steel T-nuts DIN 508 are also available without thread. They can be adapted for special applications in this way.

3.7

3.8

3.9

How to order (With thread)

DIN 508-14-M12-NI

1	a
2	d
3	Material

How to order (Without thread)

DIN 508-18-NI

1	a
3	Material

