



elesa
Original design VRTP+IR



2 Bore code

- B** Without keyway
- K** With keyway DIN 6885-1 P9

4 Type

- R** With revolving retractable handle

1 d_1	3 d_2 H7 Bore	b	d_3	d_4	d_5	l_1	l_2	l_3	r	\emptyset Handle
80	8	10	18	20,5	25	17	35	45	29	15,5
100	10	12	20	20,5	25,5	17	37	60	37	18
125	12	14	22	26	31	22	44	65	48	22
160	14	16	25	31	40	27	51	73	65	24
200	16	20	28	36	48,5	34	61	80	84	24
250	20	24	32	44	58	38	69	90	105	25
300	20	26	35,5	52	66	43	78	90	123	25
375*	26	-	39	70	81	43	87	90	160	25

* not available from stock, requires a minimum order quantity

Specification

Wheel body

- Plastic, Polypropylene (PP)
- Reinforced, shock-resistant
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Hub bushing

Steel, blackened

Cover

- Aluminum
- Anodized, natural color
- Self-adhesive
- Plastic, Polyester (PBT) for $d_1 = 375$
- Gray, shiny finish

Retractable handle

- Plastic, Polyamide (PA)
- Black, matte finish
- Retracting mechanism / Spindle
- Steel, blackened

RoHS

Elegant design and ergonomic requirements are realised for the handwheels with retractable handle GN 522.3.

When the handle is required in an operating position it is firmly anchored. To fold it in, it has to be pulled out of the arrest position parallel to the shaft. A pressure spring will hold the handle in either rest position.

see also...

GN 522.6 Handwheels with Retractable Handle (Retracting Mechanism Stainless Steel) Page QVX

Technical Information

Keyways DIN 6885-1 QVX
 ISO Fundamental Tolerances QVX
 Cross holes GN 110 QVX
 Plastic Characteristics QVX

Accessory

GN 184 Countersunk Washers (for Axial Fastening) QVX

How to order

GN 522.3-200-B20-R

- | | |
|----------|-----------|
| 1 | d_1 |
| 2 | Bore code |
| 3 | d_2 |
| 4 | Type |