



<div>1</div> <div>3</div> <div>d₁</div>	d ₂ H7	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	r	Ø Handle
80	8	18	20,5	25	18	17	35	45	29	16
100	10	18	20,5	25,5	20	17	37	60	37	18
125	12	22	26	31	22	22	44	65	48	22
160	14	26	31	40	25	27	51	80	65	23
200	16	30	36	48,5	28	34	61	80	84	24

Specification

- Plastic
Technopolymer (Polypropylene PP)
 - FDA certified
 - Reinforced, shock-resistant
 - Temperature resistant up to 80 °C
 - Black, matte finish
- Hub bushing
Stainless steel AISI 304
- Hub cover
 - Stainless steel AISI 304
 - Self-adhesive
- Revolving handle
 - Plastic, Technopolymer (Polyamide PA)
 - Black, matte finish, FDA certified
 - Spindle
Stainless steel AISI 304
- Keyway P9 DIN 6885 Page 1 → Page 2078
- Cross Holes GN 110 → Page 2080
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Elegant design taking account of ergonomic and hygienic requirements are the outstanding features of spoked handwheels GN 522.5.

Owing to the materials used, they are especially suitable for use in cor-rosive atmospheres or in areas which must be wet cleaned. In particular, the FDA certified plastic materials allow the use in the food industry.

see also...

- Stainless Steel Countersunk Washers GN 184.5 (for Axial Fixing)
→ Page 1090

How to order	1 d ₁
	2 Bore code
	3 d ₂
	4 Type
GN 522.5-125-B12-R	