


Mounting example



- 3 Type**
- S** With cylinder head screw DIN 912
 - K** With adjustable hand levers

1 **2**

d ₁	l ₂	d ₂	d ₃	d ₄	l ₁	l ₃	l ₄	l ₅	l ₆	h ₁	h ₂	Swivel clamp mounting k-dimension
M 4	16	7,5	6,9	7,5	22	11,5	4,5	4	4	18,5	23	16
M 5	20	9	8,4	9	30	14	6	5	5	24,5	30,5	20
M 6	25	10,5	9,9	10,5	45	18,5	6,5	7	6	24,5	35	25
M 6	30	10,5	9,9	10,5	45	23,5	6,5	7	6	24,5	35	30

Specification

- Handle
Zinc die casting
Powder coated
Silver, RAL 9006, textured finish
- Threaded insert, distance sleeve, centering bushing, threaded bushing
Stainless steel AISI 303
- Socket cap screw DIN 912
Stainless steel AISI 304
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

With clamping kits GN 511.1 swivel mounting clamps GN 482, T-swivel mounting clamps GN 483 as well as attachment swivel mountings clamps GN 484 with the same k dimensions can be combined to mounting clamp joints.

The centering bushing positions and supports the swivel mounting clamps in relation to each other. During assembly, the knurled threaded bushing is inserted by the clamping screw itself and by pressing into one of the two swivel mounting clamps and is then used to clamp the articulated joint.

The appropriate clamping kits are indicated in the dimensional tables of the various swivel mounting clamps.

How to order

GN 511.1-M5-20-S

1	d ₁
2	l ₂
3	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

