






- 2 Type**
- RG** With plastic knurled knob GN 7336
 - KG** With wing plastic knob
 - HG** With plastic lever
 - SG** With stainless steel star knob
 - KGN** With stainless steel wing knob
 - HGN** With stainless steel lever



3 4

h_1	Latch arm distance A															h_2	s max.
30	18	22	26	30	32	34	36	38	40	42	46	50	52	62	40	20	
50	38	42	46	50	52	54	56	58	60	62	66	70	72	82	60	40	

Specification

- Lock housing
Stainless steel **NI**
- AISI 316 (at $h_1 = 30$)
- AISI 303 (at $h_1 = 50$)
- Plain **BL**
- Latch arm
Stainless steel AISI 304
- Operating elements
- Type SG
Stainless steel AISI 304
Sheet metal drawn and hub welded
- Type KGN, HGN
Stainless steel AISI CF-8
- Type RG, KG, HG
Plastic (Polyamide PA)
Black, matte finish
- Other parts
Stainless steel AISI 304
- Protection class IP 65
- IP Protection Classes → Page QVX
- RoHS

Information

Latches GN 515 are identical to standard latches GN 115 except for the extended housing. They are operated with a rotation limited to 90°, which moves the latch arm into the locked position behind the frame. The bevels of the latch arm ease the closing of the door.

Thanks to the stainless steel material, the latches are optimally suited for use in corrosive environments.

By installing latch arms with different bend profiles, the latch distance A can be varied from 18 to 82 mm depending on the housing height h_1 , while the extended housing is suitable for a door thickness s up to 40 mm.

Latches GN 515 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page XYZ

How to order

1	Material
2	Type
3	h_1
4	Latch arm distance A
5	Finish

GN 515-NI-KGN-50-62-BL