



elesa
Original design VRTP-P+IR-SST



2 Bore code

- B** Without keyway
- K** With keyway

4 Type

- R** With revolving handle

d₁	d₂ H7	b	d₃	d₄	d₅	l₁	l₂	l₃	r	Ø Handle
80	8	18	18	20,5	25	17	35	45	29	15,5
100	10	20	18	20,5	25,5	17	37	60	37	18
125	12	22	22	26	31	22	44	65	48	22
160	14	25	26	31	40	27	51	73	65	23
200	16	28	30	36	48,5	34	61	80	84	24

Specification

Wheel body

- Plastic, Polypropylene (PP)
- Reinforced, shock-resistant
- Operating temperature 0 °C to +80 °C
- FDA compliant material
- Black, matte finish

Hub bushing

Stainless steel AISI 304

Cover

Stainless steel AISI 304
Self-adhesive

Retractable handle

- Plastic, Polyamide (PA)
- FDA compliant material
- Black, matte finish
- Retracting mechanism
- Stainless steel AISI 304
- Spindle
- Stainless steel AISI 316L

RoHS

Elegant design taking account of ergonomic and hygienic requirements are the outstanding features of the handwheels with retractable handle GN 522.6.

Owing to the materials used, they are especially suitable for use in corrosive atmospheres or in areas which must be wet cleaned. In particular, the FDA certified plastic materials allow the use in the food industry.

The handle in these handwheels is locked in the bore. To lift, first pull the handle out of the cone in axial direction.

A pressure spring keeps the handle in both positions. When folding out, it will automatically engage again.

see also...

GN 522.3 Handwheels with Retractable Handle (Retracting Mechanism Steel) QVX

Technical Information

Keyways DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 184.5 Countersunk Washers (for Axial Fastening) QVX

How to order

1 d₁
2 Bore code
3 d₂
4 Type

GN 522.6-125-K12-R

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

