



elisa
Original design B.193 p



GN 529

d ₁	d ₂		Length l						d ₃	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	9
15	M 5	-	10	16	25	-	-	-	11	11	9
18	M 5	-	10	16	25	40	-	-	13	12	9
22	M 6	-	10	16	20	25	30	40	15	14	10
25	M 6	M 8	16	25	-	-	-	-	19	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12
35	M 8	-	25	40	-	-	-	-	27	23	15



GN 529.5

d ₁	d ₂		Length l						d ₃	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	9
15	M 5	-	10	16	25	-	-	-	11	11	9
18	M 5	-	10	16	25	-	-	-	13	12	9
22	M 6	-	10	16	20	25	30	-	15	14	10
25	M 6	-	16	25	-	-	-	-	19	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12

Specification

- Plastic
Duroplast (PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- **GN 529**
Threaded stud
Steel zinc plated, blue passivated
- **GN 529.5**
Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics → Page 2158*
- *Stainless Steel Characteristics → Page 2166*
- RoHS

Information

The surface quality of the knurled screws GN 529 / GN 529.5 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible.

How to order (Threaded stud steel)

1	d ₁
2	d ₂
3	Length l

GN 529-25-M8-16

How to order (Threaded stud stainless steel)

1	d ₁
2	d ₂
3	Length l

GN 529.5-18-M5-16